



A	Skin	Size
	38.5" x 38.5"	W
		H
Diamond		Diamond Shown as it will appear on the Xpressions unit

B	Skin	Size
	28.5" x 28.5"	W
		H
1x1 Single Twist		1x1 Single Twist Shown as it will appear on the Xpressions unit

C	Skin	Size
	28.5" x 28.5"	W
		H
1x1 Single Twist		1x1 Single Twist Shown as it will appear on the Xpressions unit

D	Skin	Size
	30" x 28"	W
		H
1x1 Horizontal Thread		1x1 Horizontal Thread Shown as it will appear on the Xpressions unit

E	Skin	Size
	30" x 28"	W
		H
1x1 Horizontal Thread		1x1 Horizontal Thread Shown as it will appear on the Xpressions unit

F	Skin	Size
	30" x 28"	W
		H
1x1 Horizontal Thread		1x1 Horizontal Thread Shown as it will appear on the Xpressions unit

G	Skin	Size
	28.5" x 28.5"	W
		H
1x1 Single Twist		1x1 Single Twist Shown as it will appear on the Xpressions unit

H	Skin	Size
	28.5" x 28.5"	W
		H
1x1 Single Twist		1x1 Single Twist Shown as it will appear on the Xpressions unit

I	Skin	Size
	30" x 28"	W
		H
1x1 Horizontal Thread		1x1 Horizontal Thread Shown as it will appear on the Xpressions unit

J	Skin	Size
	55.5" x 28"	W
		H
2X1 Flat		2X1 Flat Shown as it will appear on the Xpressions unit

K	Skin	Size
	55.5" x 28"	W
		H
2X1 Flat		2X1 Flat Shown as it will appear on the Xpressions unit

It is recommended that all text and borders be 2" from the finish size

Focus Area Key
 focus area is always 3"-5" inside edge of all four sides on all skin styles and sizes
 see xpressions-snap.com for details