



A	Skin	Size
	57.5" W x 57.5" H	2x2 Flat Shown as it will appear on the Xpressions unit

B	Skin	Size	C	Skin	Size
	28.5" W x 28.5" H	1x1 Single Twist Shown as it will appear on the Xpressions unit		28.5" W x 28.5" H	1x1 Single Twist Shown as it will appear on the Xpressions unit

D	Skin	Size	E	Skin	Size
	28.5" W x 28.5" H	1x1 Single Twist Shown as it will appear on the Xpressions unit		28.5" W x 28.5" H	1x1 Single Twist Shown as it will appear on the Xpressions unit

F	Skin	Size	G	Skin	Size
	28" W x 56" H	1x2 Single Twist Shown as it will appear on the Xpressions unit		28" W x 56" H	1x2 Single Twist Shown as it will appear on the Xpressions unit

H	Skin	Size
	30" W x 28" H	1x1 Horizontal Thread Shown as it will appear on the Xpressions unit

I	Skin	Size
	30" W x 28" H	1x1 Horizontal Thread Shown as it will appear on the Xpressions unit

J	Skin	Size	K	Skin	Size
	28.5" W x 28.5" H	1x1 Single Twist Shown as it will appear on the Xpressions unit		28.5" W x 28.5" H	1x1 Single Twist Shown as it will appear on the Xpressions unit

L	Skin	Size
	30" W x 28" H	1x1 Horizontal Thread Shown as it will appear on the Xpressions unit

M	Skin	Size
	30" W x 28" H	1x1 Horizontal Thread Shown as it will appear on the Xpressions unit

N	Skin	Size	O	Skin	Size
	28.5" W x 28.5" H	1x1 Single Twist Shown as it will appear on the Xpressions unit		28.5" W x 28.5" H	1x1 Single Twist Shown as it will appear on the Xpressions unit

It is recommended that all text and borders be 2" from the finish size

Focus Area Key
 focus area is always 3"-5" inside edge of all four sides on all skin styles and sizes
 see xpressions-snap.com for details